

## Ixef® FC-1022

### polyarylamide

Ixef® FC-1022 is a 50% glass-fiber reinforced, general purpose polyarylamide compound that exhibits very high strength and rigidity, outstanding surface gloss, and excellent creep resistance.

Ixef® FC-1022 meets FDA regulations for Ixef® FC-1022 NT 000 (natural) and Ixef® FC-1022 BK 001 (black) based on clearances granted by FCN 001242 for repeated use food contact applications with all food types, under FDA conditions of use B

through H as described in Tables 1 and 2 of 21 CFR 176.170(c).

Ixef® FC-1022 is also cleared for food contact use by European Union regulations. For specific clearances, please contact your Syensqo representative.

- Black: FC-1022 BK 001
- Natural: FC-1022 NT 000

#### General

Material Status	• Commercial: Active	
Availability	<ul style="list-style-type: none"> <li>• Africa &amp; Middle East</li> <li>• Asia Pacific</li> <li>• Europe</li> </ul>	<ul style="list-style-type: none"> <li>• Latin America</li> <li>• North America</li> </ul>
Filler / Reinforcement	• Glass Fiber, 50% Filler by Weight	
Features	<ul style="list-style-type: none"> <li>• Chemical Resistant</li> <li>• Creep Resistant</li> <li>• Food Contact Acceptable</li> <li>• General Purpose</li> <li>• Good Dimensional Stability</li> <li>• Good Sterilizability</li> </ul>	<ul style="list-style-type: none"> <li>• High Flow</li> <li>• High Strength</li> <li>• Low Moisture Absorption</li> <li>• Outstanding Surface Finish</li> <li>• Ultra High Stiffness</li> </ul>
Uses	<ul style="list-style-type: none"> <li>• Appliances</li> <li>• Food Service Applications</li> </ul>	<ul style="list-style-type: none"> <li>• High Gloss Applications</li> <li>• Hospital Goods</li> </ul>
Agency Ratings	<ul style="list-style-type: none"> <li>• EU 10/2011</li> <li>• FDA 21 CFR 176.170(c)<sup>1</sup></li> </ul>	<ul style="list-style-type: none"> <li>• NSF STD-51<sup>2</sup></li> </ul>
RoHS Compliance	• RoHS Compliant	
Appearance	• Black	• Natural Color
Forms	• Pellets	
Processing Method	• Injection Molding	

Physical	Dry	Conditioned Unit	Test method
Density	1.64	-- g/cm <sup>3</sup>	ISO 1183
Molding Shrinkage	0.10 to 0.30	-- %	ISO 294-4
Water Absorption (24 hr, 23°C)	0.16	-- %	ISO 62

# Ixef® FC-1022

## polyarylamide

Mechanical	Dry	Conditioned	Unit	Test method
Tensile Modulus	19500	19500	MPa	ISO 527-1
Tensile Stress (Break)	280	260	MPa	ISO 527-2
Tensile Strain (Break)	1.9	2.2	%	ISO 527-2
Flexural Modulus	18500	--	MPa	ISO 178
Flexural Stress	380	--	MPa	ISO 178

Impact	Dry	Conditioned	Unit	Test method
Notched Izod Impact	110	--	J/m	ASTM D256
Unnotched Izod Impact	850	--	J/m	ASTM D4812

Thermal	Dry	Conditioned	Unit	Test method
Deflection Temperature Under Load 1.8 MPa, Unannealed	230	--	°C	ISO 75-2/A
CLTE – Flow	1.5E-5	--	cm/cm/°C	ISO 11359-2

Additional Information	Dry	Conditioned	Unit
Moisture Absorption – Equil, 65% RH	--		

Injection	Dry	Unit
Drying Temperature	120	°C
Drying Time	0.50 to 1.5	hr
Rear Temperature	250 to 260	°C
Front Temperature	260 to 290	°C
Nozzle Temperature	260 to 290	°C
Processing (Melt) Temp	280	°C
Mold Temperature	120 to 140	°C
Injection Rate	Fast	

# Ixef® FC-1022

## polyarylamide

### Injection Notes

Hot runners: 250°C to 260°C (482°C to 500°F)

#### Storage

Ixef® compounds are shipped in moisture-resistant packages at moisture levels according to specifications. Sealed, undamaged bags should be preferably stored in a dry room at a maximum temperature of 50°C (122°F) and should be protected from possible damage. If only a portion of a package is used, the remaining material should be transferred into a sealable container. It is recommended that Ixef® resins be dried prior to molding following the recommendations found in this datasheet and/or in the Ixef® processing guide.

#### Drying

The material as supplied is ready for molding without drying. However, if the bags have been open for longer than 24 hours, the material needs to be dried. When using a desiccant air dryer with dew point of -28°C (-18°F) or lower, these guidelines can be followed: 0.5-1.5 hour at 120°C (248°F), 1-3 hours at 100°C (212°F), or 1-7 hours at 80°C (176°F).

#### Injection Molding

Ixef® FC-1022 compound can be readily injection molded in most screw injection molding machines. A general purpose screw is recommended, with minimum back pressure.

The measured melt temperature should be about 280°C (536°F), and the barrel temperatures should be around 250 to 260°C (482 to 500°F) in the rear zone, gradually increasing to 260 to 290°C (500 to 554°F) in the front zone. If hot runners are used, they should be set to 250 to 260°C (482 to 500°F).

To maximize crystallinity, the temperature of the mold cavity surface must be held between 120 and 140°C (248 and 284°F). Molding at lower temperatures will produce articles that may warp, have poor surface appearance, and have a greater tendency to creep. Set injection pressure to give rapid injection. Adjust holding pressure and hold time to maximize part weight. Transfer from injection to hold pressure at the screw position just before the part is completely filled (95-99%).

### Notes

Typical properties: these are not to be construed as specifications.

<sup>1</sup> FDA conditions of use B through H as described in Tables 1 and 2 of 21CFR 176.170(c).

<sup>2</sup> Only IXEF® FC-1022 BK001 has been NSF STD-51 certified.

## www.syensqo.com

Safety Data Sheets (SDS) are available by emailing us or contacting your sales representative. Always consult the appropriate SDS before using any of our products.

Neither Syensqo nor any of its affiliates makes any warranty, express or implied, including merchantability or fitness for use, or accepts any liability in connection with this product, related information or its use. Some applications of which Syensqo's products may be proposed to be used are regulated or restricted by applicable laws and regulations or by national or international standards and in some cases by Syensqo's recommendation, including applications of food/feed, water treatment, medical, pharmaceuticals, and personal care. Only products designated as part of the Solviva® family of biomaterials may be considered as candidates for use in implantable medical devices. The user alone must finally determine suitability of any information or products for any contemplated use in compliance with applicable law, the manner of use and whether any patents are infringed. The information and the products are for use by technically skilled persons at their own discretion and risk and does not relate to the use of this product in combination with any other substance or any other process. This is not a license under any patent or other proprietary right.

All trademarks and registered trademarks are property of the companies that comprise the Syensqo or their respective owners.

© 2024 2023 Syensqo. All rights reserved.

