

KetaSpire® KT-880FP

polyetheretherketone

KetaSpire® KT-880FP is the high-flow grade of unreinforced polyetheretherketone (PEEK) supplied in a natural color fine powder form for compression molding and other uses that can benefit from the fine powder form.

KetaSpire® PEEK is produced to the highest industry standards and is characterized by a distinct combination of properties, which include excellent wear resistance, best-in-class fatigue resistance,

ease of melt processing, high purity, and excellent chemical resistance to organics, acids, and bases.

These properties make it well-suited for applications in healthcare, transportation, electronics, chemical processing, and other industrial uses.

The resin is also available as KetaSpire KT-880 NT in a natural-color pellet form for injection molding.

General

Material Status	 Commercial: Active 	
Availability	 Africa & Middle East Asia Pacific Europe	Latin America North America
Features	 Autoclave Sterilizable Biocompatible Chemical Resistant Ductile E-beam Sterilizable Ethylene Oxide Sterilizable Fatigue Resistant Flame Retardant Good Dimensional Stability Good Impact Resistance 	 Good Sterilizability Heat Sterilizable High Flow High Heat Resistance Radiation (Gamma) Resistant Radiation Sterilizable Radiotranslucent Steam Resistant Steam Sterilizable
Uses	 Aircraft Applications Connectors Dental Applications Electrical/Electronic Applications Film Hospital Goods Industrial Applications 	 Medical Devices Medical/Healthcare Applications Oil/Gas Applications Pump Parts Seals Surgical Instruments
Agency Ratings	• ISO 10993	• ISO 10993-1
RoHS Compliance	 RoHS Compliant 	
Appearance	• Black	Natural Color
Forms	• Pellets ¹	
Processing Method	Extrusion Blow MoldingFiber (Spinning) ExtrusionFilm ExtrusionInjection Molding	 Machining Profile Extrusion Thermoforming Wire & Cable Extrusion

Physical	Typical Value	Unit	Test method
Density / Specific Gravity	1.30		ASTM D792
Melt Mass-Flow Rate (MFR) (400°C/2.16 kg)	36	g/10 min	ASTM D1238
Molding Shrinkage ²			ASTM D955
Flow : 0.318 mm	1.4 to 1.6	%	
Across Flow : 3.18 mm	1.5 to 1.7	%	
Water Absorption (24 hr)	0.10	%	ASTM D570
Particle Size - D50	30.0 to 45.0	μm	
Mechanical	Typical Value	Unit	Test method
Tensile Modulus	/		
3	3700	МРа	ASTM D638
	4000	МРа	ISO 527-1/1A/1
Tensile Stress			
Yield	102	МРа	ISO 527-2/1A/50
4	100	MPa	ASTM D638
Tensile Elongation			
Yield ⁵	5.2	%	ASTM D638
Yield	5.0	%	ISO 527-2/1A/50
Break ⁵	10 to 20	%	ASTM D638
Break	10 to 20	%	ISO 527-2/1A/50
Flexural Modulus			
	3800	MPa	ASTM D790
	3900	MPa	ISO 178
Flexural Strength			
	153	MPa	ASTM D790
	134	MPa	ISO 178
Compressive Strength	123	MPa	ASTM D695
Shear Strength	95.1	MPa	ASTM D732
Poisson's Ratio	0.37		ASTM E132
Impact	Typical Value	Unit	Test method
Notched Izod Impact	, ,		
	53	J/m	ASTM D256
	4.9	kJ/m²	ISO 180
Unnotched Izod Impact	No Break		ASTM D4812
	NO BIECK		ISO 180
Hardness	Typical Value	Unit	Test method
Rockwell Hardness (M-Scale)	102		ASTM D785

Thermal	Typical Value Unit	Test method
Deflection Temperature Under Load		ASTM D648
1.8 MPa, Annealed	160 °C	
Glass Transition Temperature	147 °C	ASTM D3418
Peak Melting Temperature	343 °C	ASTM D3418
CLTE - Flow (-50 to 50°C)	5.0E-5 cm/cm/°C	ASTM E831
Specific Heat		DSC
50°C	1330 J/kg/°C	
200°C	1930 J/kg/°C	
Thermal Conductivity	0.25 W/m/K	ASTM E1530
Electrical	Typical Value Unit	Test method
Surface Resistivity	> 1.9E+17 ohms	ASTM D257
Volume Resistivity	3.8E+17 ohms·cm	ASTM D257
Dielectric Strength (3.00 mm)	15 kV/mm	ASTM D149
Dielectric Constant		ASTM D150
60 Hz	3.10	
1 kHz	3.01	
1 MHz	3.07	
Dissipation Factor		ASTM D150
60 Hz	1.0E-3	
1 kHz	1.0E-3	
1 MHz	3.0E-3	
Fill Analysis	Typical Value Unit	Test method
Melt Viscosity (400°C, 1000 sec^-1)	150 Pa·s	ASTM D3835

Additional Information

The particle size distribution is such that no particle is larger than 149 microns, and less than 2% of the weight of the material is larger than 106 microns.

Typical Value Unit	
150 °C	
4.0 hr	
355 °C	
365 °C	
370 °C	
375 °C	
175 to 205 °C	
Fast	
2.5:1.0 to 3.5:1.0	
	150 °C 4.0 hr 355 °C 365 °C 370 °C 375 °C 175 to 205 °C Fast

KetaSpire® KT-880FP

polyetheretherketone

Notes

Typical properties: these are not to be construed as specifications.

- ¹ Pellets are supplied lightly dusted with the lubricant calcium stearate (0.01% level). For non-lubricated, natural color grade, order KT-880 NL.
- ² 5" x 0.5" x 0.125"
- 3 1.0 mm/min
- 4 51 mm/min
- ⁵ 50 mm/min

www.syensqo.com

Safety Data Sheets (SDS) are available by emailing us or contacting your sales representative. Always consult the appropriate SDS before using any of our products.

Neither Syensqo nor any of its affiliates makes any warranty, express or implied, including merchantability or fitness for use, or accepts any liability in connection with this product, related information or its use. Some applications of which Syensqo's products may be proposed to be used are regulated or restricted by applicable laws and regulations or by national or international standards and in some cases by Syensqo's recommendation, including applications of food/feed, water treatment, medical, pharmaceuticals, and personal care. Only products designated as part of the Solviva® family of biomaterials may be considered as candidates for use in implantable medical devices. The user alone must finally determine suitability of any information or products for any contemplated use in compliance with applicable law, the manner of use and whether any patents are infringed. The information and the products are for use by technically skilled persons at their own discretion and risk and does not relate to the use of this product in combination with any other substance or any other process. This is not a license under any patent or other proprietary right.

All trademarks and registered trademarks are property of the companies that comprise the Syensqo or their respective owners.

© 2024 2023 Syensqo. All rights reserved.

