

Radel® R-5500

polyphenylsulfone

Radel® R-5500 is a general purpose extrusion grade of polyphenylsulfone (PPSU), offering exceptional hydrolytic stability and better toughness than most commercially available high-temperature polymers. This resin has a high heat deflection temperature, excellent thermal stability, outstanding resistance to environmental stress cracking, good electrical properties and inherent flame retardant properties. Transparent and opaque colors are available.

Transparent Grades:

- Natural: Radel® R-5500 NT

Opaque Grades:

- Black: Radel® R-5500 BK937
- Bone: Radel® R-5500 NT15
- Grey: Radel® R-5500 GY1137
- Grey: Radel® R-5500 GY1037
- Grey: Radel® R-5500 GY874
- Red: Radel® R-5500 RD1018
- Orange: Radel® R-5500 OR1145
- Yellow: Radel® R-5500 YL1337
- Green: Radel® R-5500 GN1007
- Blue: Radel® R-5500 BU1027
- Blue: Radel® R-5500 BU391
- Violet: Radel® R-5500 VT2582
- Brown: Radel® R-5500 BN1164

General

Material Status	• Commercial: Active	
Availability	• Asia Pacific • Europe	• Latin America • North America
Features	• Acid Resistant • Autoclave Sterilizable • Base Resistant • Biocompatible • Chemical Resistant • E-beam Sterilizable • Ethylene Oxide Sterilizable • Flame Retardant • Good Sterilizability • Good Thermal Stability	• Heat Sterilizable • High ESCR (Stress Crack Resist.) • High Heat Resistance • Hydrolytically Stable • Radiation (Gamma) Resistant • Radiation Sterilizable • Radiotranslucent • Steam Resistant • Steam Sterilizable • Ultra High Toughness
Uses	• Aerospace Applications • Aircraft Applications • Dental Applications • Food Service Applications • Hospital Goods	• Medical Devices • Medical/Healthcare Applications • Membranes • Surgical Instruments
Agency Ratings	• ISO 10993	
RoHS Compliance	• RoHS Compliant	
Automotive Specifications	• ASTM D6394 SP0311	
Appearance	• Black • Clear/Transparent	• Colors Available
Forms	• Pellets	
Processing Method	• Blow Molding • Extrusion • Film Extrusion • Injection Molding	• Machining • Profile Extrusion • Sheet Extrusion • Thermoforming

Radel® R-5500

polyphenylsulfone

Physical	Typical Value	Unit	Test method
Density / Specific Gravity	1.29		ASTM D792
Melt Mass-Flow Rate (MFR) (365°C/5.0 kg)	12 to 17	g/10 min	ASTM D1238
Molding Shrinkage - Flow (3.18 mm)	0.70	%	ASTM D955
Water Absorption			ASTM D570
24 hr	0.37	%	
Equilibrium	1.1	%	
Mechanical	Typical Value	Unit	Test method
Tensile Modulus (3.18 mm)	2340	MPa	ASTM D638
Tensile Strength (3.18 mm)	69.6	MPa	ASTM D638
Tensile Elongation			ASTM D638
Yield, 3.18 mm	7.2	%	
Break, 3.18 mm	60 to 120	%	
Flexural Modulus (3.18 mm)	2410	MPa	ASTM D790
Flexural Strength (5.0% Strain, 3.18 mm)	91.0	MPa	ASTM D790
Impact	Typical Value	Unit	Test method
Notched Izod Impact (3.18 mm)	690	J/m	ASTM D256
Tensile Impact Strength (3.18 mm)	399	kJ/m ²	ASTM D1822
Thermal	Typical Value	Unit	Test method
Deflection Temperature Under Load			ASTM D648
1.8 MPa, Unannealed, 3.18 mm	207	°C	
Glass Transition Temperature	220	°C	ASTM E1356
CLTE - Flow (3.18 mm)	5.6E-5	cm/cm/°C	ASTM D696
Electrical	Typical Value	Unit	Test method
Volume Resistivity	9.0E+15	ohms-cm	ASTM D257
Dielectric Strength			ASTM D149
0.0254 mm	> 200	kV/mm	
3.18 mm	15	kV/mm	
Dielectric Constant (3.18 mm, 60 Hz)	3.44		ASTM D150
Flammability	Typical Value	Unit	Test method
Flame Rating ¹ (0.76 mm)	V-0		UL 94
Optical	Typical Value	Unit	Test method
Refractive Index	1.672		ASTM D542
Additional Information	Typical Value	Unit	
Steam Sterilization - w/ Morpholine ²	> 1000	Cycles	

Radel® R-5500
polyphenylsulfone

Injection	Typical Value	Unit
Drying Temperature	149	°C
Drying Time	2.5	hr
Processing (Melt) Temp	360 to 391	°C
Mold Temperature	138 to 163	°C
Screw Compression Ratio	2.2:1.0	

Extrusion	Typical Value	Unit
Drying Temperature	171	°C
Drying Time	4.0	hr
Cylinder Zone 1 Temp.	338 to 388	°C
Cylinder Zone 2 Temp.	338 to 388	°C
Cylinder Zone 3 Temp.	338 to 388	°C
Cylinder Zone 4 Temp.	338 to 388	°C
Cylinder Zone 5 Temp.	338 to 388	°C
Adapter Temperature	327 to 371	°C
Melt Temperature	343 to 399	°C
Die Temperature	327 to 371	°C

Notes

Typical properties: these are not to be construed as specifications.

¹ These flammability ratings are not intended to reflect hazards presented by these or any other materials under actual fire conditions.

² Cycles passed without cracking, crazing, or rupture.

Steam Autoclave Conditions:

- Temperature: 270°F (132°C)
- Time: 30 minutes/cycle
- Steam Pressure: 27 psig (0.19 MPa)
- Stress Level: 1000 psi (7.0 MPa) in flexure
- Additive: Morpholine at 50 ppm

www.syensqo.com

Safety Data Sheets (SDS) are available by emailing us or contacting your sales representative. Always consult the appropriate SDS before using any of our products.

Neither Syensqo nor any of its affiliates makes any warranty, express or implied, including merchantability or fitness for use, or accepts any liability in connection with this product, related information or its use. Some applications of which Syensqo's products may be proposed to be used are regulated or restricted by applicable laws and regulations or by national or international standards and in some cases by Syensqo's recommendation, including applications of food/feed, water treatment, medical, pharmaceuticals, and personal care. Only products designated as part of the Solviva® family of biomaterials may be considered as candidates for use in implantable medical devices. The user alone must finally determine suitability of any information or products for any contemplated use in compliance with applicable law, the manner of use and whether any patents are infringed. The information and the products are for use by technically skilled persons at their own discretion and risk and does not relate to the use of this product in combination with any other substance or any other process. This is not a license under any patent or other proprietary right.

All trademarks and registered trademarks are property of the companies that comprise the Syensqo or their respective owners.

© 2024 2023 Syensqo. All rights reserved.

